


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DEDIMENTIAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART#	DESCRIPTION	WEIGHT
NK6TM**	8 POSITION, 8 WIRE UNIVERSAL MODULE. TERMINATION CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	1.43 LB/100 PCS (649g/100 PCS)



PANEL OPENING REQUIREMENTS
PANEL THICKNESS: .048" - .058"
(1.22mm - 1.47mm)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND PACKAGE QUANTITY.
2. MATERIAL:
MODULE HOUSING- ABS
NOMINAL WALL THICKNESS .078(2.0).
PRESERVATION CAP-PC
3. ALL NETKEY CAT6, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION PAIR MODULAR PLUGS WITHOUT DAMAGE.
4. THIS PART IS DESIGNED FOR USE WITH STANDARD KEYSTONE OPENINGS.
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ACTUAL SIZE

PART NUMBER		NK6TM* *		
TITLE		NETKEY CATEGORY 6 JACK MODULE		
CUSTOMER DRAWING				
ITEM REVISION NAME		M01336EJ/00		
DATASET FILE NAME		M01336EJ_DC41/00B		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		 MATERIAL: SEE NOTE 2		
.X ± .001 [.025] .XX ± .03 [.8] 		.XXX ± .010 [.3] ANGLES ± THIRD ANGLE PROJECTION		
DRAWN BY		DATE	CHK	SCALE
MDJR		5-06-03	REFR	NONE
				SHT 1 OF 1
				SIZE A

D10100DA/14