


## Mounting Pole

φ50 (φ40)

SZ-60L  
SZ-80L




Includes SZ-012

SZ-60T



Includes SZ-011




φ60

SZ-70L



Includes SZ-013




φ70

SZ-50L




Includes SZ-013



SZ-50T



Includes SZ-010




□70

SZ-40L




Includes SZ-013



SZ-40T



Includes SZ-010




φ81

SZ-30L



Includes SZ-013

Can not use Rubber Gasket.




SZ-30T



Includes SZ-010

Can not use Rubber Gasket.



| Model  | Material      |                   |           |              |          |                        |
|--------|---------------|-------------------|-----------|--------------|----------|------------------------|
|        | Upper bracket | Pole              | L Bracket | Cord bushing | Circular | For                    |
| SZ-80L | ABS resin     | Carbon steel pipe | SPHC      | 6/6 nylon    | —        | LCE-W                  |
| SZ-60L | ADC12         |                   | SPHC      | 6/6 nylon    | —        | LE-W                   |
| SZ-60T | —             |                   | —         | —            | ADC12    | LES-AW                 |
| SZ-70L | ABS resin     | Carbon steel pipe | SPHC      | EPT          | —        | LME-W                  |
| SZ-50L | ADC12         |                   | SPHC      | EPT          | —        | LU7                    |
| SZ-50T | —             |                   | —         | —            | ADC12    | LHE-A                  |
| SZ-40L | ADC12         | Carbon steel pipe | SPHC      | EPT          | —        | KUS                    |
| SZ-40T | —             |                   | —         | —            | ADC12    |                        |
| SZ-30L | —             |                   | SPHC      | EPT          | —        |                        |
| SZ-30T | ABS resin     | —                 | —         | —            | ADC12    | RLE,RU<br>RH,PS<br>PES |


ADC12 ··· Aluminum alloy die-cast SPHC ··· Hot rolled mild (sheet) steel  
EPT ··· Ethylene propylene rubber

## Rubber Gasket

SZ-200A



SZ-210




| Model   | Material                  | For                         |
|---------|---------------------------|-----------------------------|
| SZ-200A | Ethylene propylene rubber | KX, RH(B)                   |
| SZ-210  |                           | RU, RLE, PS(F),<br>PSX, PES |

## Tripod stand



SZ-009




| Model  | For                         | Height        |
|--------|-----------------------------|---------------|
| SZ-009 | Pitch diameter<br>φ120~φ140 | 1,285~2,285mm |


## Upper Bracket For LU7



(For  $\phi 21.7\text{mm}$  Pole)




**SZ-50NPT**  
(For  $\frac{1}{2}$ " NPT Pole)




## Upper Bracket For LU7

**SZ-60-U**  
(For  $\phi 21.7\text{mm}$  Pole)




**SZ-60NPT**  
(For  $\frac{1}{2}$ " NPT Pole)



## Pole

**Steel Pole**




800mm : **POLE-800S21**

300mm : **POLE-300S21**

100mm : **POLE-100S21**

**Aluminum Pole**




800mm : **POLE-800A21**

300mm : **POLE-300A21**


100mm : **POLE-100A21**

## NPT Adapter

**SZ-904**




**SZ-903**




## Mounting Bracket


**SZ-010**  
(For  $\phi 21.7\text{mm}$  pole)




**SZ-011**  
(For  $\phi 17.3\text{mm}$  pole)




**SZ-016A**  
(For  $\phi 21.7\text{mm}$  pole)



**SZ-70-B**  
(For  $\phi 21.7\text{mm}$  Aluminum Pole Only)



**SZ-014**




| Model   | Material                | For                               |
|---------|-------------------------|-----------------------------------|
| SZ-010  | Aluminum alloy die-cast | STD, RUP, LME, LMS, LHE           |
| SZ-011  |                         | LCE, LCS, LE, LES-A               |
| SZ-016A |                         | LU5, LU7, STD, RUP, LME, LMS, LHE |
| SZ-70-B | Cold rolled mild steel  |                                   |
| SZ-014  |                         | LE, LES-A                         |

# Optional Parts


## Wall Mount Bracket

- Bracket is detachable from machinery by loosening a screw and taking off the connectors.
- Bracket can be removed or installed upside-down during transportation.
- Wiring should not be exposed.
- Silver color type: available with special order.

Before...



After...



## How to install



Drill a hole on the mounting surface of machinery.



Fix a mounting part and connector on the hole.




Join the connectors.





Hook the mounting bracket to the metal part by tightening with a screw.

SZ-020 (For  $\phi 21.7\text{mm}$  pole)

SZ-021 (For  $\phi 17.3\text{mm}$  pole)



Mounting dimensions






Wire connector  
(SZ-020-001)  
sold separately

## Wall Mount Bracket




SZ-017

(For  $\phi 21.7\text{mm}$  Pole)





SZ-005C





SZ-012

Pole is not included





SZ-007




SZ-013





Pole is not included



SZ-008




SZ-023



| Model   | Material                 | For                                                     |
|---------|--------------------------|---------------------------------------------------------|
| SZ-017  | Aluminum alloy die-cast  | LME, STD, RUP                                           |
| SZ-018  | PBT/ABS resin            | LU7, LHE                                                |
| SZ-028  |                          | LME                                                     |
| SZ-020  | ABS resin                | LU5, LU7, LME, LMS, RUP, STD                            |
| SZ-021  |                          | LC, LCS, LE, LES-A                                      |
| SZ-005C | Electro-galvanized steel | LCE                                                     |
| SZ-007  |                          | LU7, LHE-A Pitch diameter $\phi 50, 70$                 |
| SZ-008  |                          | Pitch diameter $\phi 50, 70, 120, 140$ and $\square 74$ |
| SZ-023  |                          |                                                         |
| SZ-012  | Hot rolled mild steel    | LCE, LCS, LE, LES                                       |
| SZ-013  |                          | LME, STP, ME, MP                                        |

# Replacement Bulbs

| Model                                                                                             | Bulb No. | Wattage  | Part No.   |
|---------------------------------------------------------------------------------------------------|----------|----------|------------|
| <br>RP35/BA15S   | 1        | 12V35W   | D01203501  |
|                                                                                                   | 2        | 24V35W   | D02403501  |
| <br>RP35/BA15D   | 5        | 48V35W   | D04803502  |
|                                                                                                   | 6        | 120V40W  | D12004002A |
| <br>G18/BA15S    | 8        | 6V3W     | D00600303  |
|                                                                                                   | 9        | 12V10W   | D01201003A |
|                                                                                                   | 10       | 24V10W   | D02401003A |
|                                                                                                   | 11       | 48V10W   | D04801003  |
|                                                                                                   | 12       | 12V5W    | D01200503A |
| <br>T20/E12    | 13       | 30V10W   | D03001006A |
|                                                                                                   | 14       | 110V10W  | D11001006A |
|                                                                                                   | 15       | 220V10W  | D22001006A |
|                                                                                                   | 16       | 110V15W  | D11001506A |
|                                                                                                   | 17       | 220V15W  | D22001506A |
| <br>G14/BA9S   | 18       | 12V6W    | D01200604  |
|                                                                                                   | 19       | 24V6W    | D02400604  |
| <br>T10/E10    | 22       | 110V3W   | D11000307  |
|                                                                                                   | 23       | 110V5W   | D11000507  |
|                                                                                                   | 24       | 220V3W   | D22000307  |
|                                                                                                   | 26       | 240V5W   | D24000507  |
|                                                                                                   | 27       | 12V0.11A | D012/1107  |
|                                                                                                   | 28       | 24V0.11A | D024/1107  |
| <br>RP35/BA15D | 36       | 120V40W  | D12004024  |
|                                                                                                   | 37       | 220V30W  | D22003024  |
|                                                                                                   | 38       | 240V30W  | D24003002  |

| Model                                                                                             | Bulb No. | Wattage | Part No.     |
|---------------------------------------------------------------------------------------------------|----------|---------|--------------|
| <br>S25/BA15S   | 42       | 12V23W  | D01202305    |
|                                                                                                   | 43       | 24V25W  | D02402505    |
| <br>T10/BA15S   | 44       | 12V55W  | D01205515-02 |
|                                                                                                   | 45       | 24V70W  | D02407015-02 |
| <br>T20/E12    | 46       | 140V10W | D14001006    |
| <br>G18/BA15S | 54       | 12V15W  | D01201503    |
|                                                                                                   | 55       | 24V20W  | D02402003    |