



LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				C	REV & REDRAWN PER 0720-0040-93	3-24-93	AMP DAP

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	Listed
6 AWG SOLID OR STRANDED	6 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
6 AWG SOLID OR STRANDED	NOT APPLICABLE

1

 STAMP AMP 6* APPROX AS SHOWN

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX			36807		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			VOLTAGE RATING: NOT APPLICABLE			PART NO		
FOR APPLICATION TOOLING INFORMATION			WIRE CROSS SECTIONAL AREA RANGE: 10.5-16.8MM² [20,800-33,100] CIR MILS SOLID OR STRANDED			NAME		
FOR ORDER ENTRY			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			TERMINAL, RING TONGUE, SOLISTRAND™		
PRODUCT INFORMATION CENTER 1-800-522-6752			DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -			AMP Incorporated Harrisburg, PA 17105-3608		
TOOLING ASSISTANCE CENTER 1-800-722-1111			MATERIAL COPPER PER ASTM B-152 ANNEALED			SIZE		
1-800-526-5142			FINISH TIN PLATE 0.00254[0.00100] MIN THK PER MIL-T-10727			CAGE CODE 00779		
			DR 3-24-93 TA BRINKMAN			DRAWING NO C=36807		
			CHK 3-24-93 DA PATTERSON			SCALE 4:1		
			APPD 3-24-93 DE MILLER			SHEET 1 OF 1		
			APPD 3-24-93 JL MECKLEY					
			PRODUCT SPEC -					
			APPLICATION SPEC -					
			WEIGHT -					