


3.5mm Jack Stereo w/ 2 NC Switches

161-379US-E



3.5mm Jack Stereo w/ 2 NC Switches



DIMENSIONS: mm

ELECTRICAL SPECIFICATIONS

| | |
|--------------------------------------|--------------------------|
| Contact Resistance: | 30m ohms max. |
| Insulation Resistance: | 100M ohm min. at DC 500V |
| Dielectric Withstand Voltage: | AC 500V for one minute |

| No. | Description | Material | Quantity | Finish |
|-----|------------------|-------------|----------|---------------|
| 1 | Earth Terminal | 0.3T Brass | 1 | Silver Plated |
| 2 | Ring Spring | 0.25T Brass | 1 | Silver Plated |
| 3 | Shunt Terminal A | 0.3T Brass | 1 | Silver Plated |
| 4 | Shunt Terminal B | 0.3T Brass | 1 | Silver Plated |
| 5 | Tip Spring | 0.25T Brass | 1 | Silver Plated |
| 6 | Housing | PBT | 1 | Black Color |
| 7 | Cover | PBT | 1 | Black Color |
| 8 | Barrel | Brass | 1 | Nickel Plated |
| 9 | Spring L | SUS-304 | 1 | - |
| 10 | Spring S | SUS-304 | 1 | - |
| 11 | Metal Shell | 0.3T Brass | 1 | Nickel Plated |

Date Last Revised: 07/17/12

RoHS Compliant

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301424

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-379US-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-379US-E](#)