


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
E	B	F	EBD0-0463-04	08DEC04	RS	MG
		F1	REVISED PER ECO-09-020689	24AUG09	KK	AEG


NOTES:

- 1 FOR STRIP VERSION SEE DWG. 164153.
2 UNDERCOATING: 1,3 μ m Ni.
SELECTIVE : 0,8 μ m Au.
ZONE I : BRIGHT TIN PLATED.
3 UNDERCOATING: 1,3 μ m Ni.
SELECTIVE : 0,8 μ m Au.
REMAINDER : GOLDFLASH.
4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



WIRE RANGE :
24-20 AWG 0,20-0,56 mm²
INSULATION RANGE :
1,57 DIA. MAX.

STAINLESS STEEL	SEE NOTE 2	BRASS	164169-4
	PRETINNED		164169-3
	POST TINPLATED		4 164169-2
	SEE NOTE 3		164169-1
MATERIAL OF SLEEVE	PLATING OF BODY	MATERIAL OF BODY	PARTNUMBER

DIMENSIONS:		DWN	6 JAN 1993		MATERIAL		FINISH	
mm		CHK	J.v.LIEMPT	08-02-93	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	C.v.TILBURG	08-02-93				
		APVD	L.v.SOEST	08-02-93				
0 PLC	± -	PRODUCT SPEC			NAME HDR SOCKET CONTACT TYPE XI (CRIMP SNAP-IN) L.P.			
1 PLC	± -	—						
2 PLC	± -	APPLICATION SPEC			SIZE			
3 PLC	± -	—						
4 PLC	± -	—			CAGE CODE		DRAWING NO	
ANGLES	± -	WEIGHT			A4		00779	
		CUSTOMER DRAWING			SCALE		SHEET	
					—		1 of 1	
							REV F1	