





PART NUMBER	ITEM ① BODY	ITEM ② BASE	ITEM ③ CRIMP SLEEVE
142-0004-3D1	BRASS GOLD PL .00001 MIN OVER NICKEL PL .00005 MIN OVER COPPER PL .00005 MIN	BRASS GOLD PL .00001 MIN OVER NICKEL PL .00005 MIN OVER COPPER PL .00005 MIN	COPPER GOLD PL .00001 MIN OVER NICKEL PL .00005 MIN OVER COPPER PL .00005 MIN
142-0004-3D6	BRASS NICKEL PL .0001 MIN OVER COPPER PL .00005 MIN	BRASS NICKEL PL .0001 MIN OVER COPPER PL .00005 MIN	COPPER NICKEL PL .0001 MIN OVER COPPER PL .00005 MIN



- NOTES:
- SPECIFICATIONS:
CABLE ACCEPTABILITY: RG 316/U DOUBLE SHIELDED
RG 188/U DOUBLE SHIELDED
CABLE HEX CRIMP SIZE: .151
CABLE RETENTION: 20 LBS MIN OR CABLE BREAKING STRENGTH



CABLE STRIP DIMENSIONS



MOUNTING HOLE LAYOUT

DRAWING NO.	C - 142-0004-301/310
0	REVISIONS
ENGINEERING RELEASE	
1	6-12-92 R H S A E C O 41Q80

CUSTOMER DRAWING

THIS DRAWING TO BE INTERPRETED
PER ANSI Y 14.5M - 1982

" μ STATION"

COMPANY CONFIDENTIAL

TOLERANCE UNLESS OTHERWISE SPECIFIED	DRAWN BY VET	DATE 5-8-92	 299 Johnson Ave. P.O. Box 1732 Waseca, MN 56093-0832	
DECIMALS .XX	CHECKED BY	DATE	TITLE CABLE TERMINATION, RA PC MOUNT RG 316 DOUBLE SHIELDED	
.XXX	APPROVED BY VET	DATE 6-15-92		
MATL	APPROVED BY TAK/RJB	DATE 6-15-92	CODE NO.	DRAWING NO. C - 142-0004-301/310
FINISH	RELEASE DATE		SCALE 10:1	U/M INCH SHEET 2 OF 2