

1. ELECTRICAL SPECIFICATIONS:
CENTER FREQUENCY = 1592 ± 25 MHz
RIGHT HAND CIRCULAR POLARIZATION
3:1 VSWR B.W. = 175MHz MIN.
GAIN SHALL BE 3dBic MIN. @ CF
A/R SHALL BE 6dB MAX. @ CF
 $Z_{IN} = 50$ OHMS
2. 100% ELECTRICAL TEST PRIOR TO DELIVERY.
3. FOOTPRINT AND ELECTRICAL SPECIFICATIONS ARE SUBJECT TO CHANGE.

