



RECOMMENDED
CABLE STRIPPING DIM'S



REV.	DATE	ECR NO.	DESCRIPTION
A	01/07/97	-	MODIFY BODY (HOLES AND CUT PIN)
B	03/07/97	-	MODIFY BODY LENGTH AND STRIPPING LENGTH
C	09/11/97	-	REVISE SHELL LENGTH/ Ø4.3 HOLE DIA.
D	01/07/09	-	UPDATE DRAWING FORMAT/ INCREASE LENGTH OF 16 HEX

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
8						DRAWN	GRS	01/07/09											
7						CHECKED													
6											PART DESCRIPTION UHF TWIST-ON PLUG								
5	BODY	BRASS	SILVER	1															
4	CONTACT PIN	BRASS	GOLD	1															
3	INSULATOR	PTFE	NATURAL	1							PART NO. 182124								
2	SHELL	BRASS	SILVER	1															
1	BODY	BRASS	SILVER	1															
					CAD FILE C:/182/182124.DWG					DWG. NO.		182124.DWG		REV.	D	SIZE	A	SCALE	NA