




Passive - 2 wire
16 Channel
Output
GE Fanuc






Passive - 2 wire
16 Channel
Output Fused* w/LED and MOV
GE Fanuc



Passive - 2 wire
16 Channel
Output Fused* w/MOV
GE Fanuc



RS PLC GE9030 16PT 2x8	RS PLC DO W/BFI & MOV	RS PLC DO W/F & MOV
998189 120 VAC IC693MDL340	998001 IC693MDL740	996572 IC693MDL740
998064 24 VDC IC693MDL740, 742		
998069 24 VDC IC693MDL741		
See Above	24 VDC	24 VDC
3.0 A per channel / 3.0 A per group of 8 / 6.0 A per module	1.5 A per channel / 3.0 A per group of 8 / 6.0 A per module	1.5 A per channel / 3.0 A per group of 8 / 6.0 A per module
(1) 1 x 20 pin IDC	(1) 1 x 20 pin IDC	(1) 1 x 20 pin IDC
No	Yes	No
0°C...+50°C	0°C...+50°C	0°C...+50°C
-20°C...+60°C	-20°C...+60°C	-20°C...+60°C
90 x 70 x 56	123 x 109 x 61	123 x 109 x 61
#26...14 AWG	#26...14 AWG	#26...14 AWG
Screw Clamp	Screw Clamp	Screw Clamp



*5 x 20 mm fuses are required.
Note: Markings vary based on I/O used.

PART NUMBER SELECTION TABLES

Weidmüller