


INDUCTOR

High Current Surface Mount

Electrical Specifications at 25°C


Parameter	Min.	Nom.	Max.	Units
Inductance	8.0	10	12	μH
Current		2.38		A
DCR		50		mΩ

SCHEMATIC



- Test Frequency 2.52 MHz
- Operating Temperature: -20°C to +85°C
- High Energy Storage
- Low resistance

Dimensions in inches (mm):



RHOMBUS P/N: **L-20200**

CUST P/N: **07/29/02**

NAME:

DATE:

SHEET: 1 OF 1