


USB3.0 B/M MOLDING TYE
(USB3.0 B/公头 成型式)
OUTER MOLD NO:HJ-CT-180
(模具编号)

1.100% Test,(Open,Short,Miss Wire)


2.Contact Resistance:2 ohm max.

3. Insulation Resistance: 10M ohm min.

4.Hi-Pot:300V DC/10ms



无PP绳3800D*2PCS



NO.	NAME	Q'TY	SPECIFICATION
⑥	TUBE	4	HEAT SHRINK TUBE BLACK OD3.0* ϕ L=6mm.
⑤	TUBE	2	HEAT SHRINK TUBE BLACK OD0.8* ϕ L=9mm.
④	OUT JACKET	25g	OUTER MOLD:45P PVC COLOR:BLACK
③	CONN	1	USB3.0 B MALE TYPE SOLDER TYPE PIN-15U" INSULATION COLOR:BLUE SHELL-NICKEL
②	CONN	1	USB3.0 A MALE TYPE SOLDER TYPE PIN-15U" INSULATION COLOR:BLUE SHELL-NICKEL
①	CABLE	1	USB3.0 [(30AWG*1P+D+AL+W)*2P+30AWG*1P+24AWG*2C+ADB PVC JACKET:BLACK OD4.8 $\pm$ 0.2

cnc Tech, LLC			
Industrial Cable and Connector Technology			
DRAWED BY	ZHONGHS	DRAWING NO.	
CHECKED BY		CUSTOMER	
APPROVAL BY		ITEM NO.	103-1030-BL-00100
DECIDE BY		DATE	2012-02-16
VERSIONS/EDITION	A/0	PROJECTION	