

DATA SHEET

KA01 FINE WIRE (PTFE) THERMOCOUPLE SENSOR**TYPE 'K'****FINE WIRE SENSOR - Type 'K'****Description**

This sensor is constructed using a 1M length PTFE wire constructed as a twisted pair. The wire used is Class 1 Type K alloys (NiCr / NiAl). A weld bead is manufactured at one end of the wire whilst the other end is terminated in a moulded miniature thermocouple plug.

Sensor Features➤ **MOULDED PLUG**

The use of a moulded plug gives a robust construction as well as providing a waterproof termination.

➤ **HIGH ACCURACY THERMOCOUPLE MATERIAL THROUGHOUT**

Type 'K' Thermocouple : Class I ($\pm 0.5^{\circ}\text{C} \pm 0.25\%$)

- **WIDE AMBIENT TEMPERATURE SPECIFICATION** : -50 TO 250 °C
- **TIME RESPONSE** (*96% of value in moving gas*) : 0.1 Secs
- **MEASUREMENT RANGE** : -50 TO 250 °C

Cross-reference for compatible instruments

Suitable instruments for use with this probe

TME PART No	DESCRIPTION	APPLICATION
MM2000	SINGLE INPUT INSTRUMENT	HIGH ACCURACY TEMPERATURE MEASUREMENT
MM2010	MAX / MIN HOLD INSTRUMENT	HIGH ACCURACY INSTRUMENT WITH MAX, MIN AND HOLD FEATURES
MM2020	DIFFERENTIAL INSTRUMENT	DUAL INPUT INSTRUMENT FOR DIFFERENTIAL MEASUREMENTS
MM2030	THERMOCOUPLE SIMULATOR	HIGH ACCURACY SIMULATOR WITH MEASUREMENT FACILITY