

## MULTI-CART® R10NF



These patented Multi-Carts® ingeniously change shape and length to carry huge amounts of equipment yet fold small for storage. They instantly transform into any of 8 configurations replacing the need for 8 different carts. The revolutionary design results in a moving machine that is very lightweight, rugged, affordable, and ergonomically efficient. Designed for professionals where speed and efficiency is crucial, these Multi-Carts® can reduce time and effort moving equipment by up to 50%. They are specifically designed to work with vehicles and airlines. 5 models are available to fit your needs. Frame telescopes 34"-52" in length with 32" foldable sides. 10"x3" no-flat rear wheels and 5"x1.25" front swivel casters. **These Multi-Carts® are now supplied with low profile and no-flat wheels for longer lasting durability.** Warranty provided through cart manufacturer. Click here to download the Multi-Cart Owners Manual

### Features

- Textured powder coat finish is extremely tough & environment friendly
- Non-skid frame bed surface resists load slippage
- Expandable frame adjusts to load size
- Spring loaded wingbolts won't vibrate out
- Caster brake
- Stair climbers
- Strong tube axels 43% lighter than solid steel
- Foldable sides rotate & lock into place by pressing release cables
- Expandable frame accommodates innumerable cargo sizes and shapes
- LOAD CAPACITY: 500 lbs.
- Cart Weight: 31 lbs.
- Shipping Weight: 32.60 lbs.
- SHIPPING BOX DIMENSIONS: 36" x 20" x 10
- Length (Compacted): 34"
- Length (Extended): 52"
- Width (Frame Bed): 13.5"
- Width (Rear Wheels): 20"
- Height (Folded): 11"
- Height (Unfolded): 40.5"
- Front Casters: 5" x 1.25" Standard - Part Number (R5CSTR/Y/B)
- Rear Wheels: 10" x 3.0" No-Flat - Part Number (R10NFLT)