


Diffuse sensors with background suppression

FHDM 12

sample drawing



* emitter axis

general data

type	background suppression
light source	pulsed red LED
sensing distance T_w	15 ... 300 mm
sensing range T_b (at T_w max.)	15 ... 300 mm
sensing range T_b (at T_w min.)	5 ... 15 mm
light indicator	LED yellow
sensing distance adjustment	mechanical, 5 turn
wave length	660 nm
suppression of reciprocal influence	yes

electrical data

response time / release time	< 1 ms
voltage supply range +Vs	10 ... 30 VDC
current consumption max. (no load)	35 mA
current consumption typ.	25 mA
voltage drop Vd	< 1,8 VDC
output function	light / dark operate
output current	< 100 mA
short circuit protection	yes
reverse polarity protection	yes

mechanical data

width / diameter	12,4 mm
height / length	35 mm
depth	35 mm
type	rectangular
housing material	die-cast zinc
front (optics)	PMMA

ambient conditions

operating temperature	-25 ... +65 °C
protection class	IP 67

sample picture



**Diffuse sensors with
background suppression****FHDM 12**

order reference	connection types	output circuit
FHDM 12N5001	cable 4 pin, 2 m	NPN
FHDM 12N5001/S35A	connector M8 4 pin	NPN
FHDM 12P5001	cable 4 pin, 2 m	PNP
FHDM 12P5001/S35A	connector M8 4 pin	PNP

onlinecomponents.com