



Model # BU-60H-*

- Compatible with all shrouded, unshrouded, or retractable 0.16" (4mm) banana plugs
- Jaw opens 0.31" (7.9 mm) max
- Material: nickel-plated steel clip; tenite acetate insulated handle
- Length: 2.23" (56.75mm)
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
- Rating: 10 Amps

Phone Tip Alligator Clip with Acetate Handle



Model # BU-60HPR-*

- Accepts standard phone tip or test prod tip
- Material: nickel-plated steel clip; tenite acetate insulated handle
- Length: 2.23" (56.75mm)

- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
- Rating: 10 Amps

Alligator Clip with Acetate Handle and Screw



Model # BU-60HS-*/BU-60CHS-*

- Compatible with all shrouded, unshrouded, or retractable 0.16" (4mm) banana plugs
- Jaw opens 0.31" (7.9 mm) max
- Material: nickel-plated steel (BU-60HS-*) or solid copper (BU-60CHS-*) clip; tenite acetate insulated handle
- Length: 2.34" (59.53mm)
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
- Federal Spec: AA59466-003 (red), AA59466-016 (black), (BU-60CHS-*)
- Rating: 10 Amps