


Modular Plug

154-7641

KOBI CONN

Modular Plug



DIMENSIONS IN

SPECIFICATIONS	
USOC Type:	RJ45, 8P8C modular
Rating:	250VAC @ 2A max.
Dielectric Withstand Voltage:	500VAC
Insulation Resistance:	500M Ω .
Termination Resistance:	35m Ω max.
Operating Temperature:	-40°C ~ +125°C
Cable ~ Plug Tensile Strength:	20 lbs. (89N) min.
Contacts:	6 μ gold plated phosphor bronze
Housing:	polycarbonate
Durability	200 mating cycles
Western Electric Type:	641

Date Last Revised: 4-21-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300633

154-7641

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-7641](#)