





**Female plug with straight solder pin
pin spacing 3.81 mm / 0.15 in 100%
protected against mismating with
codig fingers**
734-502 TO 734-520

ITEM-NO. (ITEM-NO.)	734-505
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.81
P (NO. OF POLES)	5
Height (Height / mm)	14.65
Width (Width / mm)	20.55
Depth (Depth / mm)	10.5
No. of connection Points (No. of connection Points)	5
No. of potentials (No. of potentials)	5
COLOR (COLOR)	orange
Comment (Comment)	$L = (\text{No. of poles} \times \text{Pin Spacing}) + 1,5 \text{ mm}$
Dimensions (Dimensions)	1,4 +0,1 mm