





MATERIAL: NYLON 6.6

CONDUIT SIZE (mm)	THREAD SIZE	ORDERING CODE	DIMENSIONS (mm)						
			THREAD DIAMETER A	MINIMUM BORE B	BODY A/FLATS C	THREAD LENGTH D	NOMINAL LENGTH E	NUT A/FLATS F	NUT WIDTH G
12	Pg9	YCMPB 0202	15.2	9.0	19.0	12.0	27.0	22.0	11.0
16	Pg13.5	YCMPB 0304	20.4	13.0	24.0	17.0	34.0	30.0	14.0
20	Pg21	YCMPB 0406	28.3	20.0	32.0	17.0	34.0	36.0	14.0
25	Pg29	YCMPB 0507	37.0	24.0	41.0	21.0	42.0	46.0	17.0
32	Pg29	YCMPB 0607	37.0	31.0	50.0	22.0	50.0	55.0	17.0

PROPERTIES:

IP RATING WITH RECOMMENDED KOPEX CONDUITS

OPERATING TEMPERATURE

IP 50 (NO HARMFUL INGRESS OF TALCUM POWDER UNDER VACUUM AND NO PROTECTION AGAINST INGRESS OF WATER).
-20 TO +100°C.

FITTING INSTRUCTIONS INCLUDED WITH PRODUCT AND AVAILABLE ON REQUEST - LEAFLET No. 808883

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.