




## PKI 10 A rot/red

Measuring and Testing Equipment:Sockets:4 mm system

### Product description

|                      |                                                                                                                                                                                                                                                                                   |
|----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description          | Pole terminal with claw edge and captive insulated head and insulating ring. 4 mm diameter nickel-plated brass threaded bolt with 2 mm diameter transverse hole. For insulated, non-rotating installation in equipment chassis and switchpanels with a wall thickness up to 2 mm. |
| Type                 | PKI 10 A rot/red                                                                                                                                                                                                                                                                  |
| Order No.            | 930 103-101                                                                                                                                                                                                                                                                       |
| System               | 4 mm system                                                                                                                                                                                                                                                                       |
| Housing Color        | red                                                                                                                                                                                                                                                                               |
| Other standard types | black color,<br>order no. 930 103-100;<br>blue color,<br>order no. 930 103-102;<br>yellow color,<br>order no. 930 103-103;<br>green color,<br>order no. 930 103-104;<br>yellow/green color,<br>order no. 930 103-188                                                              |

### Drawing



### Technical data

|                     |            |
|---------------------|------------|
| Type of contact     | socket     |
| Type of termination | M 4 thread |
| Rated voltage       | DC 60 V    |
| Rated current       | 35 A       |

|                                 |                   |
|---------------------------------|-------------------|
| Contact resistance              | 2 mOhm            |
| Mounting                        | screw             |
| <b>Material</b>                 |                   |
| Contact material                | brass             |
| Contact surface material        | nickel-plated     |
| Housing material                | PF                |
| <b>Environmental conditions</b> |                   |
| Temperature range               | -25 °C to +100 °C |
| <b>Inflammability class</b>     |                   |
| Housing                         | 94 V-0            |