

ADAM-5060

ADAM-5069

6-ch Relay Output Module

8-ch Power Relay Output Module with LED



ADAM-5060



Specifications

General

- **Certifications** CE
- **Connectors** 1 x Plug-in screw terminal (# 14 ~ 22 AWG)
- **Enclosure** ABS+PC
- **Power Consumption** 1.8 W (max.)

Relay Output

- **Breakdown Voltage** 500 V_{AC} (50/60 Hz)
- **Channels** 2 x form A, 4 x form C
- **Contact Rating** AC: 125 V @ 0.6 A
250 V @ 0.3 A
DC: 30 V @ 2 A
110 V @ 0.6 A
- **Insulation Resistance** 1 GΩ min. @ 500 V_{DC}
- **Relay Off Time (typical)** 2 ms
- **Relay On Time (typical)** 3 ms
- **Total Switching Time** 10 ms

Ordering Information

- **ADAM-5060** 6-ch Relay Output Module



ADAM-5069



Specifications

General

- **Certifications** CE, FCC class A
- **Connectors** 1 x Plug-in screw terminal (# 14 ~ 22 AWG)
- **Enclosure** ABS+PC
- **LED Indicator** On: Active
Off: Non-active
- **Power Consumption** 2.2 W (max.)

Relay Output

- **Breakdown Voltage** 750 V_{AC} (50/60 Hz)
- **Channels** 8 x form A
- **Contact Rating** AC: 250 V @ 5 A
DC: 30 V @ 5 A
- **Insulation Resistance** 1 GΩ @ 500 V_{DC}
- **Relay On Time (typical)** 5 ms
- **Relay Off Time (typical)** 5.6 ms

Ordering Information

- **ADAM-5069** 8-ch Power Relay Output Module w/ LED

19

Embedded Controllers

20

PC-based Controllers

21

PAC

22

Motion Control

23

RS-485 I/O

24

Ethernet I/O

25

Building Automation

26

Self-service Terminals

27

eHome Platforms