

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [52484-1210](#)
Status: **Active**
Description: 2.0 W/B CONN. IDT REC. HSG ASSY

Documents:

- [3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-51090-003 \(PDF\)](#)
[Product Specification PS-52478-001 \(PDF\)](#)
[Product Specification PS-52478-002 \(PDF\)](#)
[Product Specification PS-52484-011 \(PDF\)](#)
[Product Specification PS-52484-012 \(PDF\)](#)
- [Product Specification PS-52484-021 \(PDF\)](#)
[Product Specification PS-52484-022 \(PDF\)](#)
[Product Specification PS-53358-001 \(PDF\)](#)
[Product Specification PS-55460-001 \(PDF\)](#)
[Application Specification AS-52484-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR19980
TUV	R72090227
UL	E29179

General

Product Family	IDT and Solder Connectors
Series	52484
Crimp Quality Equipment	Yes
Product Name	Mi II™
UPC	800754367905

Physical

Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Natural
Durability (mating cycles max)	30
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	673.700/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.914µm
Plating min - Termination	0.914µm
Temperature Range - Operating	-40°C to +105°C
Wire Insulation Diameter	0.85-1.05mm
Wire Size AWG	26, 28

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Application Specification	AS-52484-001
---------------------------	--------------




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[52484Series](#)

Mates With

[51206](#) , [53313](#) , [55460](#) , [53358](#) , [53324](#) ,
[53325](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
IDT System Hand Tool	0621009900

Crimp Specification
Product Specification

CS-52484
PS-51090-003, PS-52478-001, PS-52478-002,
PS-52484-011, PS-52484-012, PS-52484-021,
PS-52484-022, PS-53358-001, PS-55460-001,
RPS-51090-002, RPS-51090-005, RPS-51090-021,
RPS-52484-002, RPS-52484-005, RPS-52484-014,
RPS-52484-015, RPS-52484-017, RPS-52484-019,
RPS-52484-020, RPS-52484-022, RPS-52484-023,
RPS-52484-024, RPS-52484-025, RPS-52484-026,
RPS-52969-004, RPS-52969-006, RPS-53358-001,
RPS-54111-005, RPS-55460-015
SD-52484-008

Sales Drawing

This document was generated on 09/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[52484-1210](#)