



**605 SERIES FOR 5mm MOUNTING HOLE**


| PART NO.     | COLOR | V <sub>F</sub> | mA | mcd† | FIG. |
|--------------|-------|----------------|----|------|------|
| 605-1111-110 | R     | 2              | 10 | 1.2  | 1    |
| 605-1211-110 | G     | 2              | 15 | 0.8  | 1    |
| 605-1311-110 | Y     | 2              | 15 | 2.0  | 1    |
| 605-2111-110 | R     | 2              | 10 | 1.2  | 2    |
| 605-2211-110 | G     | 2              | 15 | 0.8  | 2    |
| 605-2311-110 | Y     | 2              | 15 | 2.0  | 2    |

**606 SERIES FOR 6mm MOUNTING HOLE**

| PART NO.     | COLOR | V <sub>F</sub> | mA   | mcd†   | FIG. |
|--------------|-------|----------------|------|--------|------|
| 606-1111-110 | R     | 2              | 5    | 2.4    | 3    |
| 606-1211-110 | G     | 2              | 15   | 3.0    | 3    |
| 606-1311-110 | Y     | 2              | 10   | 3.7    | 3    |
| 606-1415-110 | R/G   | 2              | 5/20 | .6/1.0 | 4    |
| 606-1415-120 | R/G   | 6              | 5/20 | .6/1.0 | 4    |
| 606-1415-130 | R/G   | 12             | 5/20 | .6/1.0 | 4    |
| 606-2111-110 | R     | 2              | 5    | 2.4    | 5    |
| 606-2211-110 | G     | 2              | 15   | 3.0    | 5    |
| 606-2311-110 | Y     | 2              | 10   | 3.7    | 5    |
| 606-2415-110 | R/G   | 2              | 5/20 | .6/1.0 | 6    |
| 606-2415-120 | R/G   | 6              | 5/20 | .6/1.0 | 6    |
| 606-2415-130 | R/G   | 12             | 5/20 | .6/1.0 | 6    |

**607 SERIES FOR 7mm MOUNTING HOLE**

| PART NO.     | COLOR | V <sub>F</sub> | mA | mcd† | FIG. |
|--------------|-------|----------------|----|------|------|
| 607-1112-110 | R     | 2              | 15 | 8.0  | 7    |
| 607-1212-110 | G     | 2              | 15 | 8.0  | 7    |
| 607-1312-110 | Y     | 2              | 15 | 2.2  | 7    |
| 607-1112-120 | R     | 6              | 15 | 8.0  | 8    |
| 607-1212-120 | G     | 6              | 15 | 8.0  | 8    |
| 607-1312-120 | Y     | 6              | 15 | 2.2  | 8    |
| 607-1112-130 | R     | 12             | 15 | 8.0  | 8    |
| 607-1212-130 | G     | 12             | 15 | 8.0  | 8    |
| 607-1312-130 | Y     | 12             | 15 | 2.2  | 8    |
| 607-2112-110 | R     | 2              | 15 | 8.0  | 9    |
| 607-2212-110 | G     | 2              | 15 | 8.0  | 9    |
| 607-2312-110 | Y     | 2              | 15 | 2.2  | 9    |
| 607-2112-120 | R     | 6              | 15 | 8.0  | 10   |
| 607-2212-120 | G     | 6              | 15 | 8.0  | 10   |
| 607-2312-120 | Y     | 6              | 15 | 2.2  | 10   |
| 607-2112-130 | R     | 12             | 15 | 8.0  | 10   |
| 607-2212-130 | G     | 12             | 15 | 8.0  | 10   |
| 607-2312-130 | Y     | 12             | 15 | 2.2  | 10   |
| 607-3132-120 | R     | 6              | 15 | 8.0  | 11   |
| 607-3232-120 | G     | 6              | 15 | 8.0  | 11   |
| 607-3332-120 | Y     | 6              | 15 | 2.2  | 11   |
| 607-3132-130 | R     | 12             | 15 | 8.0  | 11   |
| 607-3232-130 | G     | 12             | 15 | 8.0  | 11   |
| 607-3332-130 | Y     | 12             | 15 | 2.2  | 11   |



Housing material: Chrome plated brass  
except for Fig. 11 (polycarbonate  
matching color of LED)

† mcd intensity of LED

Dimensions in mm [inches]