




8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
COPYRIGHT 20				20			
BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.							
PART NUMBER	REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION		
1852272-1	A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER		
1852272-2	A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER		
1852272-3	A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER		
1852272-6	A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER		
7-1852272-7	A	-	-	-	SPARE PARTS		




- △ RECOMMENDED SPARE PARTS
△ GREASE LIGHTLY
△ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE



TERMINAL NAME: 1.5mm BLADE RECEPTACLE					
TE	MANF	AMP TERMINAL - AMP CRIMP SPECS			
		CRIMP HEIGHT		WIRE SIZE	
1832351	33119-0005	PAD LTR			
-	-		A	1.30 ±0.05mm [.051±.002]	18 AWG
-	-		B	1.25 ±0.05mm [.049±.002]	20 AWG
-	-		C	-	-
-	-	D			
-	-				
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	1.88mm [.074]	F	18-20 AWG
-	-	INSUL	2.39mm [.094]	O	2.03mm MAX
WIRE STRIP LENGTH 4.34-4.72mm		TERM APPL SPEC NONE		FEED 8.64mm	APPL INSTRUCTIONS 408-8040
				SET UP GAGE 458637-1	



FEED TRACK POSITION



LOC		DIST		REVISIONS			
A	66	F	LTR	DESCRIPTION	DATE	DWN	APVD
				A PRODUCT RELEASE	JUNE2006	CMR	GB
				A1 ECR-09-006210	17MAR2009	MY	TE

-	2	2	2	2	-	3-354779-1	PIN, WIRE DISC, .3145	127
-	2	2	2	2	-	2-354779-7	PIN, WIRE DISC, .3125	126
-	-	-	REF	-	-	455749-1	GUARD WINDOW	116
-	-	REF	-	-	-	679532-1	INSERT, GUARD	115
-	1	1	1	1	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
-	1	1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
-	1	1	1	1	-	318563-1	GUARD, FRONT CHIP	89
-	1	1	1	1	-	455888-6	SPACER, CRIMPER	82
-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72
-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	71
-	1	1	1	1	-	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	-	21017-2	SCREW, DRIVE	66
-	1	1	1	1	-	986950-1	WASHER, FLAT PRECISION	64
-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
-	1	1	1	1	-	23030-1	SCR, SKT HD CAP 6-32 X .25	62
-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
-	1	1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
-	1	1	1	1	-	458537-2	PAWL, FEED	56
-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
-	2	2	2	2	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	53
-	1	1	1	1	-	21018-5	NUT, HEX, REG 6-32	52
-	1	1	1	1	-	811242-2	BUMPER, HOLD DOWN	51
-	1	1	1	1	-	690753-1	SPACER, TONKER	50
-	-	1	-	-	-	690602-6	CAM, PRE FEED, 1 5/8	49
-	-	-	-	-	-	690602-5	CAM, PRE FEED, 1 1/8	48
-	1	-	-	1	-	690501-4	CAM, POST-FEED 1 5/8	47
-	1	1	1	1	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MOCA)	46
-	1	1	1	1	-	690191-1	PLUG, NYLON	45
-	1	1	1	1	-	455673-1	RAM, SIDE FEED	44
-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	43
-	1	1	1	1	-	690124-1	WASHER, RAM (.115)	42
-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
-	1	1	1	1	-	23241-6	BALL, STEEL	40
-	1	1	1	1	-	690170-1	SPRING, COMPRESSION	39
-	1	1	1	1	-	690142-1	DISC, INSULATION	38
-	1	1	1	1	-	354777-1	WIRE DISC, ASSEMBLY	37
-	1	1	1	1	-	22480-5	SPRING, COMPRESSION	36
-	1	1	1	1	-	690212-1	POST, RAM	35
-	1	1	1	1	-	690786-6	TERMINAL SUPPORT	34
-	2	2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
-	1	1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
-	1	1	1	1	-	1320908-1	SPACER, STRIP GUIDE	30
-	1	1	1	1	-	1633091-2	ASSEMBLY, STRIP GUIDE	29
-	1	1	1	1	-	1-455888-0	SPACER, CRIMPER	28
-	1	1	1	1	-	1320928-3	PLATE, STRIP GUIDE	24
-	1	-	-	1	-	690472-2	STRIPPER	22
-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
-	4	4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
-	-	1	1	-	-	691353-1	STRIPPER	19
-	1	-	-	-	-	679625-1	SHEAR HOLDER, FRONT (NO CUT)	17
-	1	1	1	1	-	3-22280-3	SPRING, COMPRESSION	12
-	1	1	1	1	-	690461-1	STOP, SHEAR	11
-	-	1	1	1	-	690459-1	SHEAR HOLDER, FRONT	10
-	1	1	1	1	-	1-454276-9	FLOATING SHEAR, FRONT	9
1	1	1	1	1	-	7-1633116-0	ANVIL, COMBINATION	8
-	1	1	1	1	-	1-455889-4	DEPRESSOR, SHEAR	5
-	1	1	1	1	-	238011-7	BLOCK, CRIMPER SPACER	4
1	1	1	1	1	-	5-683454-6	CRIMPER, INSULATION O	3
-	1	1	1	1	-	455888-9	SPACER, CRIMPER	2
1	1	1	1	1	-	6-1633305-1	CRIMPER, WIRE PREMIUM	1

-77		-6	-3	-2	-1	U/M	PART NO	DESCRIPTION		ITEM NO
THIS IS A CUSTOMER DRAWING. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED FOR THE CUSTOMER'S USE ONLY. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS CORPORATION.							DWN C. REICHELDERFER 19MAY2006	Tyco Electronics Harrisburg, PA 17105-3608		
DIMENSIONS: INCHES							APVD T. ELBIN 19MAY2006	NAME T. BENCHOFF		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 3 PLC ±.01 1 PLC ±.01 3 PLC ±.01 4 PLC ±.0001 ANGLES ±.0001							PRODUCT SPEC -	APPLICATION SPEC -		
MATERIAL -							FINISH -	WEIGHT -		
								CUSTOMER DRAWING		
								SCALE 3:5		
								SHEET 1 OF 1		
								REV A1		

CUSTOMER VIEWABLE ASSEMBLY