



Mounting: Ø.380(9.65) hole. Supplied with internal tooth lock washer and hex nut.

Wire Leads: Neon Models: No. 18 AWG (105°C) 4.4 (111.8)/4.8
(121.9) long, stripped .43 (10.9)/.57 (14.5)
LED Models: No. 22 AWG (105°C) 4.4 (111.8)/4.8
(121.9) long, stripped .43 (10.9)/.57 (14.5)

Lens: Polycarbonate

Bezel: Polished stainless steel.

Gaskets: Buna-N

Housing: Black Nylon

Lens Color	LED Solid State Indicator		
	Model No. for 12V	Model No. for 24V	Incorporates LED**
Red	6091M1-12V	6091M1-24V	4304H1
Green	6091M5-12V	6091M5-24V	4304H5
Yellow	6091M7-12V	6091M7-24V	4304H7
Internal Resistor (ohms)	390	1000	-

**Note: Also incorporates IN4004 (400 P.I.V.) rectifier diode. Red lead positive.