




- Marker Ties fasten and provide a surface to identify bundles at the same time.
- Can be marked with *PANDUIT* Marker Pens
- Can be custom imprinted with text, symbols or trademarks using *PANDUIT* Custom Hot Stamping Service.
- Can be marked with Computer Printable Labels.

Part Number: PLF1MA-C4Y

Product Family: *Pan-Ty*® Marker & Flag Ties - Colors

Product Line: Marker Cable Ties

RoHS Compliancy Status: Compliant

Note: PLF1MA-C4Y replaces PLF1MA-C4

Part Description: Marker Tie, Flag, 5.1", Miniature cross section

Product Type: Cable Ties

Material: Nylon 6.6

Color: Yellow

CSA Certified: Yes

UL Listed (File #E56854): No

UL Recognized (File #E56854): Yes

Length (In.):	5.1
Length (mm):	130
Width (In.):	.098
Width (mm):	2.5
CE Compliant:	Yes
Cross Section:	Miniature
Head Height (In.):	.154
Head Height (mm):	3.9
Head Width (In.):	.180
Head Width (mm):	4.6
Locking Style:	Locking
Marker Type:	Flag
Marker Write-On Area (In.):	.76 x 1.04
Marker Write-On Area (mm):	19.1 x 26.4
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	.87
Max. Bundle Diameter (mm):	22
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	18

Min. Loop Tensile Strength (N): 80

Std. Pkg. UOM: PK

Thickness (In.): .045

Thickness (mm): 1.1

Tool: GTS, GTSL, GS2B, PTS, PPTS, STS2

UOM: PC

Std. Pkg. Qty.: 100

Min. Order Qty.: 100