

KNIPEX X-CUT

Compact Diagonal Cutters, high lever transmission

Compact and light.

Powerful and precise.



73 02 160



73 05 160



73 06 160

Cuts finest strands as well as multi-core cables and piano wires.

- box-joint design
- doubly supported joint axis for heaviest duty
- high cutting capacity with very little effort thanks to the optimum coordination of cutting-edge angle and leverage ratio with laterally staggered pivot point
- 20 % less effort required compared to high-leverage diagonal cutters of the same length
- large opening width for thicker cables
- cuts precisely, even through fine copper wires
- compact, low-weight construction
- universally usable, in the assembly, maintenance and production
- chrome vanadium heavy-duty steel, forged, oil-hardened

20 % less effort required compared to high-leverage diagonal cutters of the same length. With double mounted hinged joint.

No.	EAN 4003773-	soft wire Ø mm	medium hard wire Ø mm	hard wire Ø mm	piano wire Ø mm	↔ mm	⚖ g
73 02 160	075127	4.8	3.8	2.7	2.2	160	175
73 02 160	075349	4.8	3.8	2.7	2.2	160	195

SB							
73 05 160	075134	4.8	3.8	2.7	2.2	160	175
73 05 160 SB	075356	4.8	3.8	2.7	2.2	160	195
73 06 160	075141	4.8	3.8	2.7	2.2	160	175
73 06 160 SB	075363	4.8	3.8	2.7	2.2	160	195



