





REV.	DATE	DESCRIPTION
A	08/28/98	REDIMENSION/ MODIFY CONTACT DIMENSIONS
B	06/05/03	UPDATE DRAWING FORMAT



RECOMMENDED CABLE STRIPPING DIMENSIONS



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .429"
 2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .118"

9				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	DO NOT SCALE DRAWING	APPROVALS DRAWN G.R.S. CHECKED ISSUED SHEET 1 OF 1	DATE 06/05/03	PART DESCRIPTION TNC REVERSE POLARITY CRIMP PLUG (FOR RG 8, 213/U CABLE) PART NO. 122394RP
8								
7								
6								
5								
4	FERRULE	COPPER	NICKEL	1				
3	CONTACT PIN	PHOS. BRONZE	GOLD	1				
2	INSULATOR	TEFLON	NATURAL	1				
1	BODY	BRASS	NICKEL	1				
	DESCRIPTION	MATERIAL	FINISH	QTY	CAD FILE C:/122/122394RP.DWG			
					DWG. NO.	122394RP.DWG	REV. B	SIZE A
								SCALE NA

Amphenol Connex