




MATERIAL
 BODY: NYLON 66 WITH 30% GLASS FILLED, UL FILE NO. E196894)
 FLAMMABILITY RATING: UL94V-0
 CONTACT: PHOSPHOR BRONZE

FINISH
 CONTACT: NICKEL PLATED

SPECIFICATIONS
 APPLICATION FOR 3V LITHIUM BATTERY
 INSULATOR RESISTANCE: 5000 M Ω MIN.
 OPERATION TEMPERATURE: -40°C TO +200°C
 DURABILITY: 50 CYCLES MIN
 CONTACT RESISTANCE: 30 M Ω MAX
 ROHS COMPLIANT

Date	SYM	REVISION RECORD	AUTH	DR.	CK.
9/28/07	A	ADDED "ROHS COMPLIANT"	T.B.	B.S.	
07/29/11	B	MATERIAL NYLON 66 WAS FR-NYLON	T.B.	B.S.	

Tolerance (Except as noted)	 Memory protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735			
decimal $\pm .5$ (.020)			Scale 4=1	Drawn By B.S.
Fractional $\pm .8$ (.030)	Title BR/CR 2032 COIN BATTERY HOLDER W/RETAINER ARM			
Angular $\pm 3^\circ$	Date 07/29/11	Drawing Number BS-3		