





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	*MSCP ±25%	*LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
EWG303	7.5	.220	.90	11.31	1,000	C-2V
EWG203	14.0	.115	.90	11.31	1,500	C-2V
EWG103	14.0	.220	1.70	21.32	1,500	C-2V
EWG803	28.0	.107	1.00	12.57	1,000	C-2F

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION														
					TITLE		T-1 1/2 SPECIAL GLASS WEDGE BASE														
A			DIMENSION CHANGE		7/16/02		DRAWN BY		APPV'D BY DATE		SIZE	FSCM NO.	DRAWING NO.								
			RELEASED & CANCEL GW-SPC-T1 1/2		6/5/00		L. WENGSTROM		E.D. 7/16/02		A	55335	GLASS WEDGE SPECIAL T-1 1/2								
REV. NO.			DESCRIPTION/ECO NUMBER			APPV'D DATE			- CAD DRAWING -			SCALE		RELEASED DATE		REVISION DATE		REV. NO.		SHEET	
									MANUAL REVISIONS NOT PERMITTED			NONE		6/5/00		7/16/02		A		1 OF 1	