

Technical datasheet: FT-50T-1.9A1-K480

Specifications:

Resonant Frequency	1.9kHz $\pm$ 0.5kHz
Max Resistance (Zr)	800 Ω
Capacitance	70000nF $\pm$ 30%nF

Dimensions:

Type A: (D: Ø50mm, d: Ø25mm, T: 0.23mm, t: 0.10mm)

