






Cable Ties Polyamide 6.6 standard

- T-Series in PA66 coloured

Material Data	
Material	Polyamide 6.6 (PA66)
Operating Temperature	-40 °C to +85 °C Continuous, (+105 °C for 500 h)
Flammability	UL94 V2



Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Material	Colour	Application Tool
Polyamide 6.6 Colours								
116-01816	T18R	100	2.5	22.0	80	PA66	Blue (BU)	1-3, 5
111-03008	T30R	150	3.5	35.0	135	PA66	Blue (BU)	1-3, 5
111-04800	T50R	200	4.6	50.0	225	PA66	Blue (BU)	1-10
111-05404	T50L	390	4.6	110	225	PA66	Blue (BU)	1-10
116-08016	T80R	210	4.7	55.0	355	PA66	Blue (BU)	1-10
116-05416	T80L	390	4.7	110	355	PA66	Blue (BU)	1-10
116-01815	T18R	100	2.5	22.0	80	PA66	Green (GN)	1-3, 5
111-03014	T30R	150	3.5	35.0	135	PA66	Green (GN)	1-3, 5
111-05402	T50L	390	4.6	110	225	PA66	Green (GN)	1-10
116-08015	T80R	210	4.7	55.0	355	PA66	Green (GN)	1-10
116-05415	T80L	390	4.7	110	355	PA66	Green (GN)	1-10
111-12001	T120R(E)	387	7.6	100	535	PA66	Green (GN)	6-10
116-01812	T18R	100	2.5	22.0	80	PA66	Red (RD)	1-3, 5
111-03004	T30R	150	3.5	35.0	135	PA66	Red (RD)	1-3, 5
111-04804	T50R	200	4.6	50.0	225	PA66	Red (RD)	1-10
111-05406	T50L	390	4.6	110	225	PA66	Red (RD)	1-10
116-08012	T80R	210	4.7	55.0	355	PA66	Red (RD)	1-10
116-05412	T80L	390	4.7	110	355	PA66	Red (RD)	1-10
111-12002	T120R(E)	387	7.6	100	535	PA66	Red (RD)	6-10
116-01814	T18R	100	2.5	22.0	80	PA66	Yellow (YE)	1-3, 5
111-03006	T30R	150	3.5	35.0	135	PA66	Yellow (YE)	1-3, 5
111-04805	T50R	200	4.6	50.0	225	PA66	Yellow (YE)	1-10
111-05428	T50L	390	4.6	110	225	PA66	Yellow (YE)	1-10
116-08014	T80R	210	4.7	55.0	355	PA66	Yellow (YE)	1-10
116-05414	T80L	390	4.7	110	355	PA66	Yellow (YE)	1-10
116-15014	T150R(H)	365	7.6	100	670	PA66	Yellow (YE)	6-10

All dimensions in mm. Subject to technical changes.



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.