

SABRETOOTH

HIGH PERFORMANCE WOOD SAWS

HOCHLEISTUNGS HOLZSÄGEN

SCIES A BOIS DE HAUTE PERFORMANCE

MADERA DE ALTO RENDIMIENTO SIERRAS



1 Triple edge, precision ground teeth specially designed to offer an easy start & outstanding cutting performance on both the push & pull stroke

Dreifachgeschärfte präzisionsgeschliffene Zähne, speziell entwickelt für leichtes Ansetzen und überlegende Sägleistung sowohl beim Stoß- als auch beim Zugschlag.

Dents à triple biseau à rectification de précision spécialement conçues pour offrir un départ aisé et de remarquables performances de coupe, à la traction comme à la poussée.

Dientes de sierra templados por inducción para proporcionar un afilado de mayor duración.

2 Induction hardened teeth for longer lasting sharpness

Induktionsgehärtete Zähne für lang anhaltende Schärfe.

Dentes trempées par induction pour un affûtage qui dure plus longtemps.

Dientes de sierra templados por inducción para proporcionar un afilado de mayor duración.

3 Rigid 1mm special alloy steel blade prevents whip & snagging

Robustes 1mm-Sägelblatt aus speziellem Stahlelement, das Durchhängen und Blockieren verhindert.

La lame rigide en acier allié spécial de 1 mm prévient le fléchissement et les accrochages.

La hoja rígida de acero de aleación especial de 1 mm evita la torsión y el enroscamiento de la sierra.



*First fix saw tested against UK's market leading saws in independent CATRA tests.

*Trennsäge gegen marktführende Sägen in Großbritannien im unabhängigen CATRA-Test.

*Säge premier passage testée par rapport aux scies dominantes le marché britannique dans le cadre d'essais réalisés par l'organisme indépendant CATRA.

*La primera sierra en sierras, comparadas con las sierras líderes en el mercado del Reino Unido mediante la realización de pruebas independientes CATRA.

WOOD SAWS



Sabretooth wood saws

Item Number	Length	Teeth	Blade
480301	22"	7tp / 10pr first fix	10
480302	22"	11tp / 12pr second fix	10

CONTENTS: 10 x Sabretooth wood saws.



Sabretooth wood saws display

Item Number	Length	Teeth	Blade
480301	22"	7tp / 10pr first fix	10
480302	22"	11tp / 12pr second fix	10

- Nickel plated flat steel frame for strength & corrosion protection
- 115mm throat for deep cuts
- 360° adjustable blade for intricate cutting



Coping saw

Item Number	Length	Blade
T0608	160mm 6 1/2"	3

Coping saw blades - Pack of 10

Item Number	Length	Blade
T0609	160mm 6 1/2"	10

HACKSAWS

- Heavy duty premium quality hacksaw with rubber grips for comfort & control
- Quick release blade change mechanism for convenience
- High leverage blade tensioning system for straighter cuts
- Spares blade storage in back frame for convenience
- 45 & 90° blade positions



Hacksaw - Quick change

Item Number	Length	Blade	Blade
T0614	300mm 12"	24	3

- Heavy duty, box section steel frame with aluminium handle for strength & durability
- High leverage blade tensioning system for straighter cuts
- Spares blade storage in back frame for convenience
- 45 & 90° blade positions



Hacksaw - Heavy duty

Item Number	Length	Blade	Blade
T0605	300mm 12"	24	3

- Box section steel frame with aluminium handle - tough & lightweight
- Spares blade storage in back frame for convenience
- 90° blade positions



Hacksaw

Item Number	Length	Blade	Blade
T0602 12	300mm 12"	24	3