



Terminal blocks for grounding on rail EN 50035 (DIN 46277/1 - NFC 63018)



E 10/13.P


Spacing 13 mm (512")



Type	Part number
1 wire clamp Can also be used as end stop E 10/13.P	162 855.23

E 35/14.P


Spacing 14 mm (55")



Type	Part number
1 wire clamp E 35/14 P	162 757 00

E 4/10.P

Spacing 10 mm (394")



Type	Part number
2 wire clamps Can also be used as end stop E 4/10.P	162 900 05

Characteristics


Wire size (see generalities)	Solid wire	0-16 mm ²				0-16 mm ²	0-35 mm ²				0-35 mm ²	0-6 mm ²			0-6 mm ²
	Stranded wire	0-10 mm ²				0-10 mm ²	0-35 mm ²				0-35 mm ²	0-4 mm ²			0-4 mm ²
Rated current		A	85				138					35			
Rated wire size			10 mm ²			10 mm ²	35 mm ²				35 mm ²	4 mm ²			4 mm ²
Other characteristics		Wire stripping length	Recommended screwdriver	Recommended torque	Protection	Wire stripping length	Recommended screwdriver	Recommended torque	Protection	Wire stripping length	Recommended screwdriver	Recommended torque	Protection		
		12 mm 47"	6,5 mm			17,2 mm 67"	10 mm			9 mm 37"	4 mm				

Accessories

	Type	Part number	Type	Part number	Type	Part number
Rail 32x15 Label with symbol "ground"	DIN 1 PR1 Z2 IDTBM	163 050 04 167 357 04	PR1 Z2 IDTBM	163 050 04 167 357 04	PR1 Z2 IDTBM	163 050 04 167 357 04


E 16/12.P

Spacing 12 mm (472")




E 25/12.P

Spacing 12 mm (472")




Type	Part number	Type	Part number
2 wire clamps Can also be used as end stop E 16/12.P	162 901.22	2 wire clamps Can also be used as end stop E 25/12.P	162 915.17

Terminal blocks for grounding on rail EN 50022 (DIN 46277/3 - NFC 63015)



D 6/10.P

Spacing 10 mm (394")



Type	Part number
1 wire clamp Can also be used as end stop D 6/10 P	162 920.20

DIN-VDE	UL	CSA	NFC-UTE	DIN-VDE	UL	CSA	NFC-UTE	Characteristics		DIN-VDE	UL	CSA	NFC-UTE
0-25 mm ²			0-25 mm ²	0-35 mm ²			0-35 mm ²	Wire size (see generalities)	Solid wire	0,5-10 mm ²			0,5-10 mm ²
0-16 mm ²			0-16 mm ²	0-25 mm ²			0-25 mm ²		Stranded wire	0,5-6 mm ²			0,5-6 mm ²
85				112				Rated current A		46			
16 mm ²			16 mm ²	25 mm ²			25 mm ²	Rated wire size		6 mm ²			6 mm ²
Wire stripping length	Recommended screwdriver	Recommended torque	Protection	Wire stripping length	Recommended screwdriver	Recommended torque	Protection	Other characteristics		Wire stripping length	Recommended screwdriver	Recommended torque	Protection
12 mm 47"	6,5 mm			14 mm 55"	8 mm					12 mm 47"	5 mm		

Type	Part number	Type	Part number	Accessories	Type	Part number
PR1 Z2 IDTBM	163 050.04 167 357 04	PR1 Z2 IDTBM	163 050.04 167 357 04	Rail 35x7,5 Label with symbol "ground"	DIN 3 PR3 IDTBM	164 800 03 167 357 04