




MATERIALS:

Body: Gold Plated Brass
Center Contact: Gold Plated Beryllium Copper
Dielectric: PTFE

Finish:

Body: Tarnish Resistant
Center Contact: Gold Plated

RATINGS:

Operating Temperature: -65°C (-85°F) to +165°C (+329°F)
Operating Voltage: 1000 VRMS
Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 2455

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA