

## 7 outlet, 6-ft cord, 1080 joule strip - Protect It! Surge Suppressor

MODEL NUMBER: **STRIKER**



### Description

Tripp Lite's STRIKER offers economical AC surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. AC surge suppression shields connected equipment from damage and performance problems due to transient surges. STRIKER offers 7 AC outlets, 6-ft. cord and diagnostic LEDs to warn of wiring problems and suppressor damage. AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive gray housing with keyhole mounting tabs and 1 designated transformer plug outlet offer convenient protection of desktop computer equipment and accessories. \$20,000 Ultimate Lifetime Insurance (USA & Canada only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 x NEMA5-15R/6-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 1 transformer-spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/1080 joules/400V UL1449 Let-through Rating

### Features

- 7 outlets
- 6-ft. cord
- Surge suppression rating: 1080 joules
- EMI/RFI noise filtering
- Can accommodate 1 transformer without blocking remaining outlets
- Diagnostic LED indicate protection present
- Keyhole supports for wall mounting
- \$20,000 Ultimate Lifetime Insurance (USA and Canada Only) covers connected equipment

## Specifications

### OVERVIEW

### Highlights

- 7 outlets/6-ft. cord
- 1080 joule surge suppression rating
- \$20,000 Ultimate Lifetime Insurance (USA & Canada only)

### Applications

- Ideal for any desktop, network or home computing application requiring AC line surge protection.

### Package Includes

- STRIKER Surge Suppressor
- Instruction manual with warranty information

Intended Application	Home/Office
<b>OUTPUT</b>	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	7 NEMA 5-15R
Transformer accommodation	Supports 1 large transformer plug accessory without covering remaining outlets; accepts up to 4 transformers total
Outlet orientation	Single row
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length (ft.)	6
Input cord length (m)	1.83
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	72000
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332010520
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	1080
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	400V
EMI / RFI filtering	Up to 20 dB
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No

Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping Dimensions (HWD/in)	13.78 x 4.52 x 1.77
Shipping Dimensions (HWD/cm)	35.00 x 11.48 x 4.50
Shipping weight (lbs)	1.30
Shipping weight (kg)	0.59
Unit Dimensions (HWD/in)	1.32 x 2.05 x 11.69
Unit Dimensions (HWD/cm)	3.35 x 5.21 x 29.69
Unit weight (lbs)	1.17
Unit weight (kg)	0.53
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light Gray
AC line cord color	Light Gray
Style	Strip
Outlets center to center measurement	Distance between standard outlets = 29mm; Distance between last standard outlet and transformer outlet = 33mm
Keyhole slot center to center measurement	Distance between slots = 151mm; Distance between slot height = 24mm
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
NOM (Mexico)	NOM
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 <a href="#">Ultimate Lifetime Insurance</a>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#):

[STRIKER](#)