

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

P

F

ZONE

LTR

REVISIONS

DESCRIPTION

DATE

APPD

AJ


16

0


REL PER 93-3338-009

5-3-93

MS



1. CRIMP TOOLING:
CENTER CONTACT= AMP-O-LECTRIC 565435-5
APPLICATOR= 567386-2
FERRULE= PNEUMATIC TOOL 69365-3, DIE SET 58159-1



RECOMMENDED
STRIP LENGTH

RG-188/U	2-328666-5	228905-5	414597-1
FOR USE WITH CABLE	(2) FERRULE QTY=1	(1) JACK ASSY, BHD, UHF QTY=1	PART NO

				PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm (INCHES) TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -	DR 5-3-93 M. SNEED	AMP AMP Incorporated Harrisburg, PA 17105-3608			
	CHK 5-3-93 R. HENRY				
	MATERIAL -	APPD 5-3-93 R. HENRY	NAME JACK KIT, BHD, MIN UHF		
APPD 5-3-93 M. SNEED		SIZE CAGE CODE DRAWING NO B 00779 414597			
PRODUCT SPEC -					
FINISH -	APPLICATION SPEC -	WEIGHT - SCALE 5:1 SHEET 1 OF 1			