

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) Search Tips

Text Search: 'ABMS-AT-D'

Your search criteria matched only one product, shown below

Cable ties may be inserted from either of two sides. Choose adhesive backed or screw installed mounts.

Part Number	ABMS-AT-D
RoHS Compliance Status	Compliant
Part Description	2-Way Cable Tie Entry Mount
Material	Nylon 6.6
Color	Natural
UL Recognized	E136577
Height (In.)	.21
Height (mm)	5.3
Length (In.)	1.13
Length (mm)	28.7
Width (In.)	1.13
Width (mm)	28.7
Adhesive Type	Acrylic
CE Compliant	Yes
CE Marking	Yes
Environment	Indoors / High Temp
Max. Bundle Diameter (mm)	4.8
Mounting Method	Adhesive Backed
Pricing Description	Cable Tie Mount, Hi Temp. Adh., 1.1"x1.1" (27.9mm x 27.9mm), WH
Screw Size	#6 (M3)
Screw Size Metric	M3
Used With Cable Ties	M, I, S
Min. Order UOM	PC
Min. Order Qty.	500
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	☐

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.