


## PRECISION GROUND SHOULDER SCREWS

Shoulder ground to  $+.000/-0.001$  Dia,  $+.002 /-.000$  Length. **MATERIAL:** Stainless Steel, ASTM A581/A582




SLOTTED



SOCKET

| CAT. NO. | LENGTH      | CAT. NO. |
|----------|-------------|----------|
| 2421     | .125 (3.2)  | 2441     |
| 2422     | .250 (6.4)  | 2442     |
| 2423     | .375 (9.5)  | 2443     |
| 2424     | .500 (12.7) | 2444     |




SLOTTED



SOCKET

| CAT. NO. | LENGTH      | CAT. NO. |
|----------|-------------|----------|
| 2425     | .125 (3.2)  | 2445     |
| 2426     | .250 (6.4)  | 2446     |
| 2427     | .375 (9.5)  | 2447     |
| 2428     | .500 (12.7) | 2448     |



SLOTTED




SOCKET

| CAT. NO. | LENGTH      | CAT. NO. |
|----------|-------------|----------|
| 2431     | .125 (3.2)  | 2451     |
| 2432     | .250 (6.4)  | 2452     |
| 2433     | .375 (9.5)  | 2453     |
| 2434     | .500 (12.7) | 2454     |
| 2435     | .625 (15.9) | 2455     |


## SHAFT LOCKS

**MATERIAL:** Brass, Nickel Plate


For .125 (3.2) SHAFT



CAT. NO. 1700




For .250 (6.4) SHAFT



CAT. NO. 1701



For .250 (6.4) SHAFT



CAT. NO. 1702


## .250 (6.4) SHAFT COUPLING



- Two set screws hold shaft securely

**MATERIAL:** Brass, Nickel Plate  
Set Screws: Steel, Zinc Plate  
Supplied unassembled


CAT. NO. 1453



## VOLUME CONTROL EXTENDERS



For .250 (6.4) volume control shafts having .375-32 threaded bushings.




| CAT. NO. | A           | B           |
|----------|-------------|-------------|
| 1464     | .625 (15.9) | .250 (6.4)  |
| 1465     | .625 (15.9) | .375 (9.5)  |
| 1466     | .687 (17.4) | .500 (12.7) |
| 1467     | .750 (19.1) | .250 (6.4)  |

**MATERIAL:** Brass, Nickel Plate

## PANEL BEARINGS

STANDARD and MINIATURE



**MATERIAL:** Brass, Nickel Plate  
Supplied unassembled

| CAT. NO. | A          | B (HEX)     | C           | D           | E THREAD          |
|----------|------------|-------------|-------------|-------------|-------------------|
| 1705     | .253 (6.5) | .437 (11.1) | .500 (12.7) | .437 (11.1) | .375-32 Standard  |
| 1706     | .128 (3.3) | .343 (8.7)  | .437 (11.1) | .375 (9.5)  | .250-32 Miniature |

## PANEL NUTS



For Volume Controls, Switches, Tip Jacks, etc.

| CAT. NO. | FOR           | THREAD   | DIAMETER     | THICKNESS   |
|----------|---------------|----------|--------------|-------------|
| 1448     | Mounting      | 1/4-32   | .375 Hex     | .093 (2.38) |
| 1449     | Mini. Control | 1/4-32   | .312 Hex     | .078 (1.98) |
| 1456     | Vol. Control  | 3/8-32   | .500 Hex     | .093 (2.38) |
| 1458     | Switch        | 15/32-32 | .562 Hex     | .078 (1.98) |
| 1459     | Switch Ring   | 15/32-32 | .625 Knurled | .062 (1.57) |
| 1472     | Filter        | 15/16-32 | .375 Hex     | .093 (2.38) |

**MATERIAL:** Brass, Nickel Plate