


PRIMO RANGE MULTIGRIP PLIERS


NF E 73-108 / ISO 8976 / DIN ISO 8976



Multibost


- Riveted rack joint.
- Flexible position change.
- Fitted with a wire cutter: max. 80 kg/mm².
- Finger anti-crush stop.
- 7 setting positions.
- Self-clamping on tubes.
- Orange PVC sleeves with guard.

L1	1	*	Ø	w	7 g
240	117230	1	6	-	350
240	117235	6	3	C5	370
240	117400	8	80	-	350



PRIMO RANGE DIAGONAL CUTTING PLIERS


NF E 73105 / ISO 5749 / DIN ISO 5749



Mechanics diagonal cutting pliers

- Double induction treatment of cutting edges to cut hard materials: piano wire (200 kg/mm²).
- Axis offset to cutting edges for maximum cutting demultiplication
- Orange PVC sleeves with guards.

L1	1	*	Ø	w	7 g
160	117280	6	6	-	172
160	117285	1	3	C2	192
180	117290	5	6	-	232
180	117295	0	3	C2	252



Electricians diagonal cutting pliers

- Double induction treatment of cutting edges to cut half-hard wires max 160 kg/mm².
- Axis offset towards cutting edges for maximum cutting demultiplication.
- Orange PVC sleeves with guards.

L1	1	*	Ø	w	7 g
140	117300	1	6	-	162
140	117305	6	3	C2	187
160	117310	0	6	-	197
160	117315	5	3	C3	219

* For a full EAN, add the following before the code: 303254

Bost

Catalogue 2005