







**HEADER PRESS-IN PIN 0.6x0.6 MM  
PIN SPACING 2.5 MM / 0.098 IN 100%  
PROTECTED AGAINST MISMATING  
MATING**

**733-332/100-000 TO 733-342/100-000**

**PDF DATASHEET**

© 1992 - 2011 CADENAS GmbH

|                                                      |                                      |
|------------------------------------------------------|--------------------------------------|
| ITEM-NO. (ITEM-NO.)                                  | 733-334/100-000                      |
| Measured voltage (Measured voltage / V)              | 160                                  |
| Measured shock voltage (Measured shock voltage / kV) | 2.5                                  |
| Pollution degree (Pollution degree)                  | 2                                    |
| Current intensity (Current intensity / A)            | 4                                    |
| RM (PIN SPACING / mm)                                | 2.5                                  |
| P (NO. OF POLES)                                     | 4                                    |
| Height (Height / mm)                                 | 8.9                                  |
| Width (Width / mm)                                   | 12.5                                 |
| Depth (Depth / mm)                                   | 7.8                                  |
| COLOR (COLOR)                                        | lichtgrau                            |
| Comment (Comment)                                    | L = (No. of poles + 1) x Pin Spacing |
| Dimensions (Dimensions)                              | 1,1 +0,1 mm                          |