



English | 简体中文 | 日本語

Search by Part Number

GO

Search by Keyword(s)

GO

Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Calculators | Cross Reference | Green Initiative | Parametric Search | Search by Part Number, Keyword, Document, Green/Pb-Free, Package

Home > Products > Other > Miscellaneous > 844S0258-07 > 844S0258BK-07LFT

You may also like...

844S0258BK-07LFT

Category: Miscellaneous
Generic Part: 844S0258-07
Description: MULTIRATE FEMTOCLOCK LVPE



Parameters

Package	VFQFPN 32
Speed	NA
Temperature	C
Voltage	3.3 V

Sales and Support

Sales Offices

► Sales Offices and authorized distributors

Technical Support

Clock Help
► WWW: Clock Help

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

No documents available for this part at this time.

Package

Package	VFQFPN 32 (NLG32)
Description	VFQFP-N 5 X 5 X 1.0MM NO LEAD
Status	Active
Class	PLASTIC
Category	Green
Pb (Lead) Free	Yes
Pb Free Category	e3 Sn
Mark	K
Package Type	VFQFPN
Lead Count	32
Length	5.0 mm
Width	5.0 mm
Thickness	1.0 mm
Pitch	0.5 mm
Tube / Tray	TRAY
Quantity per Tube/Tray	490
Quantity per Reel	2500
Moisture Sensitivity Level (MSL)	3
Moisture Exposure Floor Life	168hrs@<30C/60%RH
Peak Reflow Temperature	260°C
Rebake Conditions	48hrs@125C
Related Package Documents	view documents