

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1201080001

Status:


Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Ultra-Lock (M12) to Standard RJ-45 Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), 3.0m (9.84') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E200650
General	
Product Family	Industrial Cordsets
Series	120108
Connector End A	Ultra-Lock (M12)
Connector End B	RJ-45 (standard)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Industrial Ethernet Solutions
Product Name	Ultra-Lock (M12)
Protocol	N/A
Region	America, Asia, Europe
Type	Double Ended
UPC	78172501622
Physical	
Cable Diameter	6.00mm (.236")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Green
Coupling Style	Push to Lock
Gender	Male-Male
Keyway	D-coded
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-25°C to +60°C
Wire Size AWG	26
Wire/Cable Type	Shielded-Stranded
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	30V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-120108-001-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120108 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION