


Item	79D00-G080-003-RS / 79D00-G160-002-RS	79D00-G160-001-RS
SSD	Intel® SSD 2.5"	Intel® SSD 1.8"
Capacities	80GB / 160GB	160GB
Interface	Serial ATA II 3.0G	Serial ATA II 3.0G
Data Transfer Rate(max.)	Read:250MB/sec ; Write:70MB/sec	Read: 250MB/s ; Write: 70MB/s
Operation Temp.	0°C~70°C	0°C~70°C
Storage Temp.	-55°C~95°C	-55°C~95°C
Humidity	5~95% non-condensing	5~95% non-condensing
Vibration	2.17G	2.17G
Shock	1000G/0.5ms	1000G/0.5ms
MTBF	2000000 Hours	1200000 Hours
Dimension	100 x 69 x 9.5	78 x 54 x 5 mm
Certificate	UL/CE/BSMI/RoHS	UL/CE/BSMI/RoHS

New

79D00-G080-003-RS
79D00-G160-002-RS



79D00-G160-001-RS

Ordering Information


79D00-G080-003-RS	SATA II 2.5" SOLID STATE DRIVE 80GB MLC
79D00-G160-002-RS	SATA II 2.5" SOLID STATE DRIVE 160GB MLC
79D00-G160-001-RS	SATA II 1.8" SOLID STATE DRIVE 160GB MLC

Industrial DRAM Module Series

Complete product line of Industrial IEI provide complete product line of industrial Features

- Refresh → TREFI=7.8ms from -40°C~+85°C
- 30ms Gold Finger
- Stern Test of parameter
- High reliability

-40°C~+85°C
Wide Temp.
Available



DDR W/T Solution

Module Speed	400 Mhz
Long Dimm	184 Pin
SO Dimm Pin	200 Pin
CAS Latency	CL3


DDR SO-DIMM



DDR Long-DIMM (Low Profile)



DDR Long-DIMM



Ordering Information

DDR SO-DIMM W/T	Description
79300-M256-057-RS	DDR 400 256MB SO-DIMM CL3 32M*16
79300-G001-046-RS	DDR 400 1GB SO-DIMM (BGA) CL3 64M*8
79300-M512-069-RS	DDR 400 512MB SO-DIMM CL3 32M*16
DDR Long-DIMM W/T	Description
79300-G001-044-RS	DDR 400 1GB DIMM CL3 64M*8
79300-M512-070-RS	DDR 400 512MB DIMM CL3 64M*8 (Low profile)

DDR2 W/T Solution

Module Speed	667 Mhz
Long Dimm	240 Pin
SO Dimm Pin	200 Pin
CAS Latency	CL5

DDR2 SO-DIMM



DDR2 Long-DIMM (Low Profile)




Ordering Information

DDR2 SO-DIMM W/T	Description
79900-G001-023-RS	DDR2 667 1GB SO-DIMM CL5 64M*8
79900-M512-015-RS	DDR2 667 512MB SO-DIMM CL5 64M*8
79900-G002-013-RS	DDR2 667 2GB SO-DIMM CL5 128M*8
DDR2 Long-DIMM W/T	Description
79800-G001-025-RS	DDR2 667 1GB Long-DIMM CL5 64M*8 (Low profile)
79800-M512-022-RS	DDR2 667 512MB Long-DIMM CL5 64M*8 (Low profile)

DDR3 W/T Solution

Module Speed	1333 Mhz
SO Dimm Pin	204 Pin
CAS Latency	CL9

DDR3 SO-DIMM



Ordering Information **New**

DDR3 SO-DIMM W/T	Description
79B00-G001-010-RS	DDR3 1333 1GB SO-DIMM CL9 128M*8
79B00-G002-006-RS	DDR3 1333 2GB SO-DIMM CL9 256M*8