



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NO.	'A'	WEIGHT 10pcs lbs (g)
JP131SBC87RB___	0.812-0.912 [20.6-23.2]	3.00 (1360)



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PRODUCT COLOR.
- HOOK MATERIAL: NYLON 6/6
ANGLE BRACKET MATERIAL: PRE-GALVANIZED STEEL
RIVET MATERIAL: ALUMINUM
CLAMP MATERIAL: PLATED IRON
BOLT/WASHER MATERIAL: ZINC PLATED STEEL
- PRODUCT IS DESIGNED TO SUPPORT A MAXIMUM OF 1 5/16" (33.34) DIAMETER BUNDLE. MAXIMUM RECOMMENDED STATIC LOAD: 20 lbs.
- PRODUCT INCORPORATES FEATURES ALLOWING USER TO RETAIN CABLE BUNDLES IN J-PRO J-HOOK WITH TAK-TY CABLE TIES UP TO 3/4" WIDE.
- PRODUCT MARKINGS:
cULus logo and statement:
"SUITABLE FOR USE IN AIR HANDLING SPACES IN ACCORDANCE WITH SECTION 300-22 (C) & (D) OF THE NATIONAL ELECTRIC CODE."
ULC logo and statement:
"IN ACCORDANCE WITH CAN/ULC S-102.2-10 IN SINGLE UNITS OR PAIRS, 4 ft (1220mm) MIN. SPACING, FSR=0, SDC=35."

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01	1/16/14	RVU	CLW	KLN	REMOVED "-" FROM PART NUMBER	GAECN01576
00	1/31/13	DBLA	CLW	KLN	INITIAL RELEASE	GAECN00425

TITLE		J-PRO J-HOOK WITH 360° SCREW-ON BEAM CLAMP (JP131SBC87RB__)	
		CUSTOMER DRAWING	
ITEM REVISION NAME		121031AR/00	
DATASET FILE NAME		121031AR_DC_C11037/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °		SEE NOTE 2	
		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		C11037	
DRAWN BY	DATE	CHK	SCALE
DBLA	1/25/2013	KLN	NONE
		SHT 1 OF 1	
		SIZE	
		A	