


Professional Leaded Resistors



DESCRIPTION

A homogeneous film of metal alloy is deposited on a high grade ceramic body. After a helical groove has been cut in the resistive layer, tinned connecting wires of electrolytic copper are welded to the end-caps. The resistors are coated with lacquer which provides electrical, mechanical, and climatic protection. Four or five colour code rings designate the resistance value and tolerance according to **IEC 60 062**. Suitable replacements for MRS16 and MRS25 are MBA/SMA 0204 and MBB/SMA 0207 professional.

FEATURES

- Professional resistors in small outlines
- Low noise
- Lead (Pb)-free solder contacts
- Pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes
- Compatible with "Restriction of the use of Hazardous Substances" (RoHS) directive 2002/95/EC (issue 2004)




APPLICATIONS

- All general purpose applications

TECHNICAL SPECIFICATIONS		
DESCRIPTION	VALUE	
	MRS16	MRS25
Resistance Range	4.99 Ω to 1 M Ω	1 Ω to 10 M Ω
Resistance Tolerance and Series	$\pm 1\%$; E24/E96 series	
Maximum Dissipation at $T_{amb} = 70\text{ }^{\circ}\text{C}$	0.4 W	0.6 W
Thermal Resistance (R_{th})	170 K/W	150 K/W
Temperature Coefficient	$\pm 50\text{ ppm/K}$	
Maximum Permissible Voltage (DC or RMS)	200 V	350 V
Basic Specifications	IEC 60115-1 and 60115-2	
Climatic Category (IEC 60068)	55/155/56	
Max. Resistance Change for Resistance Range, ΔR max., After:		
Load:		
$R \leq 100\text{ k}\Omega$	$\pm (0.5\% R + 0.05\ \Omega)$	$\pm (0.5\% R + 0.05\ \Omega)$
$R > 100\text{ k}\Omega$	$\pm (1\% R + 0.05\ \Omega)$	$\pm (0.5\% R + 0.05\ \Omega)$
Climatic Tests:		
$R \leq 100\text{ k}\Omega$	$\pm (0.5\% R + 0.05\ \Omega)$	$\pm (0.5\% R + 0.05\ \Omega)$
$R > 100\text{ k}\Omega$	$\pm (1\% R + 0.05\ \Omega)$	$\pm (0.5\% R + 0.05\ \Omega)$
Soldering:		
$R \leq 100\text{ k}\Omega$	$\pm (0.1\% R + 0.05\ \Omega)$	$\pm (0.1\% R + 0.05\ \Omega)$
$R > 100\text{ k}\Omega$	$\pm (0.25\% R + 0.05\ \Omega)$	$\pm (0.1\% R + 0.05\ \Omega)$
Short Time Overload	$\pm (0.25\% R + 0.05\ \Omega)$	$\pm (0.25\% R + 0.05\ \Omega)$

PACKAGING				
MODEL	REEL		BOX	
	PIECES/REEL	CODE	PIECES/BOX	CODE
MRS16	5000	RP	1000 5000	C1 CT
MRS25	5000	RP	1000 5000	C1 CT

DIMENSIONS



DIMENSIONS - leaded resistor types, mass and relevant physical dimensions

TYPE	D _{max.} (mm)	L _{max.} (mm)	d _{nom.} (mm)	M _{min.} (mm)	MASS (mg)
MRS16	1.6	3.6	0.5	5.0	125
MRS25	2.5	6.3	0.6	10.0	220

12NC INFORMATION

- The resistors have a 12-digit numeric code starting with 2322 15.
- The subsequent 2 digits indicate the resistor type and packaging; see the 12NC Ordering Code table.
- The remaining 4 digits indicate the resistance value:
 - The first 3 digits indicate the resistance value.
 - The last digit indicates the resistance decade in accordance with the 12NC Indicating Resistance Decade table.

Last Digit of 12NC Indicating Resistance Decade

RESISTANCE DECADE	LAST DIGIT
1 Ω to 9.76 Ω	8
10 Ω to 97.6 Ω	9
100 Ω to 976 Ω	1
1 kΩ to 9.76 kΩ	2
10 kΩ to 97.6 kΩ	3
100 kΩ to 976 kΩ	4
1 MΩ to 9.76 MΩ	5
10 MΩ	6

12NC Example

The 12NC of a MRS16 resistor, value 750 Ω, on a bandolier of 1000 units in ammpack is: 2322 157 17501.

12NC - resistors type and packaging

TYPE	ORDERING CODE 2322 15.		
	BANDOLIER IN AMMPACK		BANDOLIER ON REEL
	1000 UNITS	5000 UNITS	5000 UNITS
MRS16	7 1....	7 2....	7 3....
MRS25	6 1....	6 2....	6 3....

PART NUMBER AND PRODUCT DESCRIPTION

PART NUMBER: MRS16000C5119FCT00

MODEL/SIZE	SPECIAL CHARACTER	TCR	VALUE	TOLERANCE	PACKAGING ⁽¹⁾	SPECIAL
MRS1600 MRS2500	0 = Neutral	C = ± 50 ppm/K	3 digit value 1 digit multiplier MULTIPLIER 7 = *10 ⁻³ 2 = *10 ² 8 = *10 ⁻² 3 = *10 ³ 9 = *10 ⁻¹ 4 = *10 ⁴ 0 = *10 ⁰ 5 = *10 ⁵ 1 = *10 ¹ 6 = *10 ⁶	F = ± 1 %	RP CT C1	Up to 2 digits 00 = Standard

PRODUCT DESCRIPTION: MRS 16-50 1 % CT 51R1

MRS16 MODEL/SIZE MRS16 MRS25	50 TCR ± 50 ppm/K	1 % TOLERANCE ± 1 %	CT PACKAGING ⁽¹⁾ RP CT C1	51R1 RESISTANCE VALUE 51R1 = 51.1 Ω 1K = 1 kΩ
---------------------------------------	-------------------------	---------------------------	--	--

Notes:

⁽¹⁾ Please refer packaging table

- The PART NUMBER is shown to facilitate the introduction of a unified part numbering system for ordering products



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.