


REV.	DATE	DESCRIPTION
NC	01/25/99	INITIAL RELEASE
A	07/28/06	UPDATE DRAWING FORMAT



NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .151"
2. CRIMPED CONTACT PIN SQ. CRIMP SIZE 0.7mm

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex							
7	HEAT SHRINK TUBE			1		DRAWN	G.R.S.	07/28/06									
6	FERRULE	COPPER	NICKEL	1		CHECKED			PART DESCRIPTION SMB BULKHEAD CRIMP JACK (FOR RG-316U/D CABLE)								
5	HEX NUT	BRASS	NICKEL	1		ISSUED											
4	LOCK WASHER	BRASS	NICKEL	1		SHEET	1 OF 1										
3	CONTACT PIN	BRASS	GOLD	1					PART NO. 142180								
2	INSULATOR	TEFLON	NATURAL	1													
1	BODY	BRASS	NICKEL	1		CAD FILE C:/142/142180.DWG			DWG. NO.		142180.DWG	REV.	A	SIZE	A	SCALE	NA