














## APPLICATION




## DIODE LASER

- APC power control
- Current stable control
- Operate Voltage: 3V-5V
- Focus Adjustable




Example: 650nm/10mW/Lines

**UM650-10-G**




## POWER SUPPLY

- Constant voltage, low ripple.
- Short circuit protection.
- Current limit protection: 100mA
- AC95V-AC125 or AC190V-AC250V switchable.




**SP-2**



## LASER HOLDER

- X-Y-TILT-θ movement



**08UMM-A**

