

BZGI-2RN34

M

DRAWING  
NUMBER

X8

ISSUE  
X4

REPLACES

PR-14257

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

REVISIONS

|    |              |
|----|--------------|
| A  | C067624      |
| 18 | SLB JUN 90   |
| B  | C072977      |
| 6  | J W 8 AUG 92 |
| C  | CO-77179-C   |
| 12 | MAM MAR 94   |

FO-92851-8

DRAWN

J A S 14 OCT 85

KAG 17 OCT 85

CHECK

CHECK



CHECK

CHECK

CHECK

CHECK

CHECK



|                                                                                                                                                                                     |                                     |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------|
| THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH. |                                     |
| CHARACTERISTICS                                                                                                                                                                     | ELECTRICAL DATA                     |
| OPERATING FORCE ----- 15-39 OZ                                                                                                                                                      | CONTACT ARRANGEMENT<br>S P D T      |
| RELEASE FORCE ----- 10 OZ MIN                                                                                                                                                       | L74                                 |
| DIFFERENTIAL TRAVEL ----- .002 MAX                                                                                                                                                  | 1/5A 125, 250, OR 480VAC 2A 600 VAC |
| OVERTRAVEL ----- .219 MIN                                                                                                                                                           | 1/8 HP 125 VAC, 1/4 HP 250 VAC      |
| SWITCH-BASIC REPLACEMENT ----- BZ-2RN7027                                                                                                                                           | 1/2A 125 VDC, 1/4A 250 VDC          |

|                                                                                                        |               |
|--------------------------------------------------------------------------------------------------------|---------------|
| SCALE FULL                                                                                             |               |
| DO NOT SCALE PRINT                                                                                     |               |
| TOLERANCES<br>APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE UNLESS NOTED. TOLERANCES ARE 2 |               |
| DIM.<br>mm                                                                                             | TOL.<br>mm/in |
| NO PLACES                                                                                              | 1/64          |
| ONE PLACE                                                                                              | 0.4/0.18      |
| TWO PLACES                                                                                             | 0.16/0.008    |
| THREE PLACES                                                                                           | 0.13/0.005    |
| DESIGN UNITS                                                                                           | SI METRIC     |
|                                                                                                        | US CUSTOMARY  |
| THIRD ANGLE PROJECTION                                                                                 |               |
| WEIGHT                                                                                                 |               |

NOTES

1 - 6-32 UNC X .219 REF BINDING HEAD TERMINAL SCREW AND CUPWASHER (3)