



LOC		DIST		ZONE		LTR		REVISONS		DATE	APPD
G	14	P	F	C	REV 8	REDRAWN PER	0720-0040-93	4-13-93	AMP		



AMP WIRE RANGE		E13288 Listed	
16-14 AWG		16-14 AWG	
SOLID OR STRANDED		SOLID OR STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
16-14 AWG		NOT APPLICABLE	
SOLID OR STRANDED			

1 STAMP AMP 16-14* APPROX AS SHOWN
2 MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE	
FOR APPLICATION TOOLING INFORMATION	1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS SOLID OR STRANDED	
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 3 PLC DEC ± ANGLES		DR 4-13-93 TA BRINKMAN	AMP AMP Incorporated Harrisburg, PA 17105-3608
MATERIAL COPPER PER ASTM B-152 ANNEALED		CHK 4-13-93 DA PATTERSON	
FINISH TIN PLATE 0.00254 [.000100] MIN THK PER MIL-T-10727		APPD 4-13-93 DE MILLER	
APPLICATION SPEC		APPD 4-13-93 JL MECKLEY	SPlice, BUTT, STRAP, SOLISTRAND™
WEIGHT			
SCALE 10:1		SIZE CAGE CODE 00779 DRAWING NO. C=322459	