




FEATURES:

- Multi-purpose test clips allow four ways to connect to a device under test
 - o U-shaped nose for blade shaped terminals
 - o Notched jaw for gripping screw heads, bare wire or terminals
 - o Serrated teeth for gripping threaded or wire wrapped terminals
 - o Cluster of sharp needles for piercing small gauge wires (#22-28 AWG)

MATERIALS:

Jaws: Non-rusting Nickel Copper Alloy.

Boot: Vinyl

Wire: 20 AWG PVC

Cable: 2 conductor, 22 AWG, 7 x 30 tc, .180" outside diameter

Y Mold: PVC

Bantam: Miniature phone plug 3 conductor, sleeve no connection

RATINGS:

Operating Voltage: Hand-held 30 VAC/60 VDC

Hands free operation in a controlled voltage environment: 300 VRMS

Current: 5 Amperes

ORDERING INFORMATION: Model 6486-60 Standard Length = 60" (1524,0)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90952 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6486-60